

Product Cut Sheet

STAND-OFF MOUNT POWER STRIP

Mounts to 19"EIA or 23" wide rack on 6.75"D (172 mm) Standoff Brackets.

- Six or eight, 3-prong, 15A or 20A, 110-125 VAC outlets
- Circuit breaker provides basic over-current protection
- Optional surge protection provides basic voltage-spike protection (1100 Joules, LED indicator)
- IEC C20 power inlet with cord retention bracket
- Includes a detachable power cord with NEMA plug
- Select a straight or locking plug
- Includes mounting brackets and installation hardware
- UL Listed



Part Number	Input			Output		Dims - in (mm)		
	Amp	kW	Plug	Breakers	Outlets	H	W	D
110-125 Volt, Single-Phase Power Strip								
12817-701	15	1.4	NEMA 5-15P	1 x 15A	(8) 5-15R	1U	19"EIA/23"	8.2 (208)
12817-702	15	1.4	NEMA L5-15P	1 x 15A	(8) 5-15R	1U	19"EIA/23"	8.2 (208)
12817-705	20	1.9	NEMA 5-20P	1 x 20A	(8) 5-20R	1U	19"EIA/23"	8.2 (208)
12817-706	20	1.9	NEMA L5-20P	1 x 20A	(8) 5-20R	1U	19"EIA/23"	8.2 (208)
110-125 Volt, Single-Phase Power Strip, Surge-Protected								
12817-703	15	1.4	NEMA 5-15P	1 x 15A	(6) 5-15R	1U	19"EIA/23"	8.2 (208)
12817-704	15	1.4	NEMA L5-15P	1 x 15A	(6) 5-15R	1U	19"EIA/23"	8.2 (208)
12817-707	20	1.9	NEMA 5-20P	1 x 20A	(6) 5-20R	1U	19"EIA/23"	8.2 (208)
12817-708	20	1.9	NEMA L5-20P	1 x 20A	(6) 5-20R	1U	19"EIA/23"	8.2 (208)

Notes: Includes 19"EIA and 23"W horizontal rack-mount standoff brackets. Standoff Brackets are 6.75"D (172 mm). The Power Strip is 1.4"D (36 mm). The power strip can be mounted at the end 8.2"D (208 mm) or edge 6.75"D (172 mm) of the standoff brackets. All power strips have IEC C20 inlets and include a power cord. Cords with locking plugs are 10'L (3 m). Cords with straight plugs are 8'2"L (2.4 m).

800-834-4969 in U.S. & Canada • www.chatsworth.com



©2013 Chatsworth Products, Inc. All rights reserved. CPI, CPI Passive Cooling, GlobalFrame, MegaFrame, Saf-T-Grip, Seismic Frame, SlimFrame, TeraFrame, Cube-iT Plus, Evolution, OnTrac, Velocity and QuadraRack are federally registered trademarks of Chatsworth Products. eConnect and Simply Efficient are trademarks of Chatsworth Products. All other trademarks belong to their respective companies.

03/2013