


INPUT PLUG DETAIL  
NEMA L6-20  
20A / 2P3W



| Technical Specs:                 |  |
|----------------------------------|--|
| <b>Input Ratings</b>             |  |
| Nominal Voltage (VAC)            | 208V 1ph   |
| Input Plug / Cord                | NEMA L6-20P (IP20), 10 ft. Cord  |
| Current Rating                   | 16A  |
| Power Rating (kW)                | 3.33   |
| <b>Output Ratings</b>            |  |
| Nominal Voltage (VAC)            | 208V   |
| Current Rating                   | 16A  |
| Outlet Rating                    | C13 10A max, C19 16A max   |
| Max Current per Breaker          | N/A Balanced; N/A Unbalanced   |
| <b>Outlet Combination</b>        |  |
| Load Segment                     | Refer to Simplified Wire Schematic   |
| PDU Total                        | (18)C13 (6)C19   |
| <b>Branch Circuit Protection</b> | (0) No Breaker   |
| <b>Features:</b>                 |  |
| Local Display                    | (1) LCD Display - Branch Monitoring, IP Setup, Alarm Notification, Auto-Oriented |
| Branch Monitoring                | Current, Voltage, Power, PF per Circuit  |
| Outlet Monitoring                | Current, Voltage, Power, PF per Outlet   |
| Monitoring Accuracy              | +/- 1% True RMS  |
| Ethernet Port                    | 10/100/1000 Mbps RJ45  |
| Remote Monitoring                | GUI, SNMP v1-3, RS232, RESTful API, Power IQ                                     |
| Remote Control                   | ON/OFF/CYCLE outlets remotely  |
| IP Consolidation                 | Link up to 32 PDUs under a single IP Address                                     |
| USB Ports (2)                    | Update firmware, Opt'l Temp/Humidity Sensor                                      |
| Controller Module                | Field Replaceable  |
| Auxiliary Port (2)               | Opt'l Front and Rear Electric Door Lock  |
| Cord Retention                   | Locking Receptacles  |
| Mounting System                  | Multiple tool-less mounting button locations, A and B (see detail)               |
| <b>Dimensions &amp; Weights:</b> |  |
| Width (In[mm])                   | 2.2[55]  |
| Height (In[mm])                  | 71.9[1827]   |
| Depth (In[mm])                   | 2.8[70.1]  |
| Weight (lbs[kg])                 | 18[8.2]  |
| <b>Regulatory Information:</b>   | NEMKO Listed to UL/IEC 62368-1, CE, RoHS, FCC Part 15 Class A, EN 55022          |
| <b>Regulatory Part Number:</b>   | K60-0D080-40F-72A  |
| <b>Environmental Conditions:</b> |  |
| Operating Temperature            | 32 - 149F (0 - 65C) @ Input Pwr Rating (kW)                                      |
| Operating Rel Humidity           | 5 - 95%  |
| Operating Elevation              | 0-10000 ft (0-3000 m)  |
| Storage Temperature              | -13 - 149F (-25 - 65C)   |
| Storage Rel Humidity             | 5 - 95%  |
| Storage Elevation                | 0-50000ft (0-15000m)   |
| <b>Hardware Included:</b>        | (2) tool-less pre-installed mounting buttons<br>(1) ground kit cable             |
| <b>Warranty:</b>                 | 3 yrs. Standard, 2 add'l yrs Opt'l   |
| <b>Optional Accessories:</b>     | Temp & Humidity Sensor, Electronic Locks   |

- Notes:
- 1 All Dimension are in inches [millimeters] unless otherwise specified
  - 2 Installation must conform with all related national and local codes
  - 3 All Bracket kits are sold separately. Toolless mounting buttons are included for installation in CPI cabinets.
  - 4 For more information, please contact Tech Support at [techsupport@chatsworth.com](mailto:techsupport@chatsworth.com)


©2019 Chatsworth Products, Inc.  
All rights reserved.

All products quoted are subject to availability based on manufacturing capacity and shipping dates should be considered estimates only.

While every effort has been made to ensure the accuracy of all information, CPI does not accept liability for any errors or omissions and reserves the right to change information and descriptions of listed services and products.



eConnect Vertical PDU, Switched Pro, C20 inlet to L6-20, 10ft (3m), 208V Single Phase Input, 20A, (18) C13 (6) C19 Outlets, 208V Output



EA-6069-X ISS  
SHEET 1 OF 1 1