PatchRack for CPI Cable Runway

P/N 13395

P/N 13394

Miniature rack for interconnect equipment attaches to overhead cable runway in the data center and saves valuable rack or cabinet space for computer and data storage equipment.

KEY FEATURES

• Attaches to all CPI cable runway (Universal, TELCO and UL), but the design is optimized for 1- 1/2"H x 3/8"W (38.1 mm x 9.53 mm) side stringers or cross members

• Attaches to cable runway in parallel or perpendicular orientation to align with the front or side of a rack or a cabinet

• Attaches above or below cable runway to provide head room (clearance) for passers-by

• Adjusts right or left to align with cable entry points in racks and cabinets

• Supports 19"W rack-mount equipment, such as patch panels

• Two heights:
  - 4U
  - 8U

• Two configurations:
  - Side Stringer
  - Cross Member

• Holds 60 lb (27.2 kg)

SPECIFICATIONS

Description	• Side Stringer Brackets attach to1-1/2"H x 3/8"W (38.1 mm x 9.53 mm) cable runway side stringers and orients patch panel bracket above or below and parallel or perpendicular to the cable runway.
	• Perpendicular orientation is limited to cable runway that is 12" (300 mm) or less in width
	• Includes (25) 12-24 equipment-mounting screws
	• Includes assembly and installation hardware, choose:
	  - Side Stringer or
	  - Cross Member Brackets

Dimensions	Cross Member Brackets attach to 3/8"H x 1-1/2"W (9.53 mm x 38.1 mm) cable runway cross members and orient patch. Add a cross member hardware kit for perpendicular orientation
	
	Overall Heights (2):
	  - 9-5/16" H (237 mm), 4U
	  - 16-5/16"H (415 mm), 8U
	• Overall Width: 19.81" (503 mm)
	• Overall Depth: 3.30" (84 mm)
	• Load bearing capacity: 60 lb (27.2 kg)

	• Supports 19"W rack-mount equipment • Formed mounting channels, front and rear equipment mounting •Threaded 12-24 equipment-mounting holes
Material	Aluminum sheet • Finish: Grained aluminum or painted black, glacier white or gray

Availability: US, Canada, Latin America, Europe, Middle East & Africa

ORDERING INFORMATION

The PatchRack is a miniature two-post rack that can be attached to CPI Cable Runway to save rack-mount space by placing patch panels or interconnect equipment above the rack or cabinet. Use PatchRack to create a zone network in the data center.

Two versions are available; Racks P/N 13395 attach to the Cable Runway side stringer with a 7"D (180 mm) standoff bracket, and Racks P/N 13394 attach to a cross member underneath the Cable Runway. The position of the rack can be adjusted front-to-back or side-to-side. Racks P/N 13395 can also attach perpendicular to Cable Runway that is 12"W (300 mm) or less. Use the Cross Member Hardware Kit P/N 13399-702 for perpendicular mounting of all racks on any width of Cable Runway.
• Attaches to all CPI Cable Runway but optimized for 1-1/2"H x 3/8"W (38.1 mm x 9.53 mm) side stringers or cross members to Universal Cable Runway
• Supports 19"W rack-mount equipment; supports up to 60 lb (27.2 kg)
• Side Stringers (P/N 13395) are compatible with all styles of CPI Runway; Cross Members (P/N 13394) are not compatible with Adjustable Cable Runway

Cable Runway Patch Panel Rack		
Part Number	Description	Shipping Weight lb (kg)
13395-X04	With Side Stringer Brackets, 4U	5 (2.3)
13395-X08	With Side Stringer Brackets, 8U	7 (3.2)
13394-X04	With Cross Member Brackets, 4U*	4 (1.8)
13394-X08	With Cross Member Brackets, 8U*	6 (2.7)

*X=color: 1=Gray, 5=Clear, 7=Black, E=Glacier White. Computer Beige kits include gold colored hardware. Gray and Black kits include black colored hardware. Does not include Side Stringer Brackets. *Attaches to Cross Member in parallel orientation only.*

Accessories For PatchRack

Use Cross Member Hardware Kit for perpendicular mounting on all widths of Cable Runway. The D-Ring Kit provides cable management.
• Not compatible with Adjustable Cable Runway

| Accessories		
Part Number	Description	Shipping Weight lb (kg)
13399-702	Cross Member Hardware Kit, Black	1 (0.5)
13396-704	D-Rings for 4U Rack, 6 Rings, Black	2 (0.9)
13396-708	D-Rings for 4U Rack, 10 Rings, Black	4 (1.8)

DIMENSIONS

4.00 Bracket
2.7 Min / 16.0 Max
1.55 Min / 5.70 Max
3.30 Depth
7.35 Max Depth
A
5/8"
1-3/4" 5/8"
18.31 Mounting Holes
17.75 Inside Rails
19.81 Overall
3.0 Width Channel
9.31 For 4 RMU
16.31 For 8 RMU Height

P/N 13395

P/N 13394

P/N 13399-X02 Shown installed on right.

P/N 13396-XXX Shown installed on left.

chatsworth.com

techsupport@chatsworth.com

800-834-4969

CHATSWORTH PRODUCTS