



CUBE-iT® Wall-Mount Cabinet

CUBE-iT® Floor-Supported Cabinet

ThinLine II Wall-Mount Cabinet

Standard Swing Gate Wall Rack

EasySwing Wall-Mount Rack

Fixed Wall-Mount Rack

Application:
Designed to secure information and communications equipment (ICT) in a telecommunications room or any public spaces where floor space is limited.

- Key Features:**
- Easy access to the front and rear of equipment with a three-part, swing-out body; EIA-310-D compliant
 - Attractive design with multiple door styles and colors make it suitable for public areas
 - Removable top and bottom panels with a rectangular knockout provide retrofit capability
 - Increased security with access to the rear only through the keyed front door
 - Variety of cable management options and accessories such as low-decibel dual-fan kit

- Heights:**
- 24" (610 mm), 12U
 - 36" (910 mm), 19U
 - 48" (1220 mm), 26U

- Depths:**
- 24" (610 mm), 12U
 - 36" (910 mm), 19U
 - 48" (1220 mm), 26U

- Load Bearing:**
- Supports 300 lb (136 kg)

- Construction:**
- Riveted and bolted; powder coat finish

Application:
A larger version of CUBE-iT Wall-Mount Cabinet to support a larger network in a telecommunications room or any public spaces where floor space is limited.

- Key Features:**
- Easy access to the front and rear of equipment with a three-part, swingout body; EIA-310-D compliant
 - Attractive design with multiple door styles and colors make it suitable for public areas
 - Deep rear panel allows top or bottom conduit termination, wheeled base assists in opening action
 - Increased security with access to the rear only through the keyed front door
 - Variety of cable management options and accessories such as low-decibel dual-fan kit

- Heights:**
- 60" (1520 mm), 33U
 - 72" (1830 mm), 40U

- Depths:**
- 24" (610 mm)
 - 30" (760 mm)

- Load Bearing:**
- Supports 1000 lb (453.6 kg)

- Construction:**
- Riveted and bolted; powder coat finish rails bolt to frame

Application:
Space-saving with minimal intrusion into the room – perfect for high-traffic, tight areas.

- Key Features:**
- Individual rails can be easily rotated for horizontal or vertical mounting and then bolted into place making patch panel punchdown easier.
 - Removable top panel provides direct access to equipment without disturbing other devices
 - Ships fully assembled with mounting hardware
 - Multiple sets of knockouts allow flexibility in cable organization
 - Cabinet includes a junction box 2" x 4" (50 mm x 100 mm) to hold optional surge-suppression duplex outlet
 - EIA-310-D compliant

- Heights:**
- 26" (660 mm)
 - 36" (910 mm)

- Depths:**
- 5" (130 mm), 2U
 - 8.5" (216 mm), 4U
 - 12" (300 mm), 6U

- Load Bearing:**
- Static load, 100 lb (45.4 kg)

- Construction:**
- Steel

Application:
Provides easy access to the rear of equipment, making it the ideal choice for supporting patch panels and switches.

- Key Features:**
- Dual hinges open to the right or left, stopping at 90°
 - Supports single- and double-sided shelves
 - Ships partially assembled with installation hardware
 - EIA-310-D compliant; rack-mount spaces are marked and numbered

- Heights:**
- 29.1" (739 mm), 12U
 - 43.1" (1095 mm), 20U
 - 53.6" (1361 mm), 26U
 - 78.1" (1984 mm), 40U

- Depths:**
- 12.2" (310 mm)
 - 18.2" (462 mm)
 - 25.2" (640 mm)

- Load Bearing:**
- Supports 100 lb (45.4 kg) in open position; can increase to 150 lb (45.4 kg) with optional kit

- Construction:**
- Steel and Aluminum

Application:
Cost-effective 19" EIA swing gate rack for mounting network, ICT and security equipment in a telecommunications or equipment room where floor space is limited.

- Key Features:**
- Opens 180° to right or left, locking latch pin secures gate in the closed position
 - Ships fully assembled and flat; simply unfold and mount to wall
 - Keyhole wall mounting holes with mounting template included on carton
 - EIA-310-D compliant

- Heights:**
- 24.5" (622 mm), 11U
 - 38.5" (978 mm), 19U
 - 51.5" (1308 mm), 26U

- Depths:**
- 8.0" (204 mm)
 - 12.0" (305 mm)
 - 18.0" (457 mm)
 - 25.0" (635 mm)

- Load Bearing:**
- 85 lb (38.6 kg)

- Construction:**
- Welded and bolted steel

Application:
Space-saving, sturdy platform for wall-mounting equipment.


- Key Features:**
- EIA-310-D compliant; rack-mount spaces are marked and numbered
 - Supports single- and double-sided shelves
 - Tapped #12-24 roll-formed threads; includes equipment mounting screws

- Heights:**
- 27.4" (696 mm), 12U
 - 41.4" (1052 mm), 20U
 - 76.4" (1361 mm), 40U

- Depths:**
- 6.6" (168 mm)
 - 12.6" (320 mm)
 - 18.6" (472 mm)

- Load Bearing:**
- Supports 200 lb (90.7 kg) of equipment; securely mounts to wall using eight leg mounting holes

- Construction:**
- Aluminum



CUBE-IT® Wall-Mount Cabinet			CUBE-IT® Floor-Supported Cabinet			ThinLine II Wall-Mount Cabinet			Standard Swing Gate Wall Rack			EasySwing Wall-Mount Rack			Fixed Wall-Mount Rack			
Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)	
11900-X24	24"H x 24"W x 24"D; 12U (610 mm x 610 mm x 610 mm) Tempered Glass Door	101 (45.8)	13492-X60	60"H x 27.3"W x 24"D (1520 mm x 693 mm x 610 mm) Solid Metal Door; 33U	248 (112.7)	13050-X11	26"H x 26"W x 5"D, 2U (660 mm x 660 mm x 130 mm), Black finish	47 (21.3)	11790-X18	29.1"H x 19"W x 17"D, 12U (739 mm x 600 mm x 430 mm)	24 (10.9)	13602-X12	24.5"H x 19"W x 10.5"D 11U, (622 mm x 600 mm x 266 mm)	24 (10.9)	11960-X06	27.4"H x 19"W x 6"D, 12U (696 mm x 600 mm x 150 mm)	9 (4.1)	
11840-X24	24"H x 24"W x 24"D; 12U (610 mm x 610 mm x 610 mm) Solid Metal Door	101 (45.8)	13495-X60	60"H x 27.3"W x 24"D (1520 mm x 693 mm x 610 mm) Tempered Glass Door; 33U	278 (126.4)	13050-X12	26"H x 26"W x 8.5"D, 4U (660 mm x 660 mm x 216 mm) Black finish	54 (24.5)	11791-X18	43.1"H x 19"W x 17"D, 20U (1095 mm x 600 mm x 430 mm)	26 (11.8)	13604-X12	38.5"H x 19"W x 10.5"D 19U, (978 mm x 600 mm x 266 mm)	24 (10.9)	11961-X06	41.4"H x 19"W x 6"D, 20U (1052 mm x 600 mm x 150 mm)	10 (4.5)	
11900-X36	36"H x 24"W x 24"D; 19U (910 mm x 610 mm x 610 mm) Tempered Glass Door	128 (58.2)	13493-X60	60"H x 27.3"W x 30"D (1520 mm x 693 mm x 760 mm) Solid Metal Door; 33U	260 (118.2)	13050-X13	26"H x 26"W x 12"D, 6U (660 mm x 660 mm x 300 mm) Black finish	60 (27.2)	11792-X18	78.1"H x 19"W x 17"D, 40U (1984 mm x 600 mm x 430 mm)	33 (15.0)	13608-X12	51.5"H x 19"W x 10.5"D 26U, (1308 mm x 600 mm x 266 mm)	24 (10.9)	11962-X06	76.4"H x 19"W x 6"D, 40U (1941 mm x 600 mm x 150 mm)	15 (6.8)	
12419-X36	36"H x 24"W x 30"D; 19U (910 mm x 610 mm x 760 mm) Tempered Glass Door	142 (64.4)	13496-X60	60"H x 27.3"W x 30"D (1520 mm x 693 mm x 760 mm) Tempered Glass Door; 33U	290 (131.8)	13050-X21	36"H x 26"W x 5"D, 2U (910 mm x 660 mm x 130 mm) Black finish	60 (27.2)	11790-X25	29.1"H x 19"W x 24"D, 12U (739 mm x 600 mm x 610 mm)	42 (19.1)	X=Color; 1=Gray, 2=Computer Beige, and 7=Black. Other sizes and styles available.	11960-X12	27.4"H x 19"W x 12"D, 12U (696 mm x 600 mm x 300 mm)	12 (5.4)			
12419-X48	48"H x 24"W x 30"D; 26U (1220 mm x 610 mm x 760 mm) Tempered Glass Door	171 (77.6)	13493-X72	72"H x 27.3"W x 30"D (1830 mm x 693 mm x 760 mm) Solid Metal Door; 40U	309 (140.5)	13050-X22	36"H x 26"W x 8.5"D, 4U (910 mm x 660 mm x 216 mm) Black finish	54 (24.5)	11791-X25	43.1"H x 19"W x 24"D, 20U (1095 mm x 600 mm x 610 mm)	46 (20.9)		11961-X12	41.4"H x 19"W x 12"D, 20U (1052 mm x 600 mm x 300 mm)	13 (5.9)			
11996-X36	36"H x 24"W x 30"D; 19U (910 mm x 610 mm x 760 mm) Solid Metal Door	142 (64.4)	13496-X72	72"H x 27.3"W x 30"D (1830 mm x 693 mm x 760 mm) Tempered Glass Door; 40U	342 (155.5)	13050-X23	26"H x 26"W x 12"D, 6U (910 mm x 660 mm x 300 mm) Black finish	60 (27.2)	11792-X25	78.1"H x 19"W x 24"D, 40U (1984 mm x 600 mm x 610 mm)	60 (27.2)	X=Color; 1=Gray, 2=Computer Beige, 7=Black and E=Glacier White. Other sizes and styles available.	11962-X12	76.4"H x 19"W x 12"D, 40U (1941 mm x 600 mm x 300 mm)	16 (7.3)			
X=Color; E=Glacier White; 7=Black. Other sizes and styles available.			X=Color; E=Glacier White; 7=Black. Other sizes and styles available.			X=Color; 1=Gray, 2=Computer Beige, and 7=Black. Other sizes and styles available.			Key Accessories				Key Accessories			Key Accessories		
Key Accessories	Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)
	40972-001	Standard Fan and Filter Kit	2 (0.9)	40972-001	Standard Fan and Filter Kit	5 (2.3)	12955-719	Fiber Slack Mgr Panel	2 (0.9)	12795-X01	Heavy-Duty Swing Gate Kit (2) Brackets	4 (1.8)	12858-001	Corner Cushions, Set of 4	1 (0.5)	12858-001	Corner Cushions, Set of 4	1 (0.5)
	40975-001	Low-Decibel Dual-Fan Kit	4 (1.8)	40975-001	Low-Decibel Dual-Fan Kit	4 (1.8)	12934-001	Surge-Suppressed Duplex Receptacle	2 (0.9)									
	40970-704	Vertical Cabling Section, 4U	5 (2.5)	40971-X60	Vertical Lashing Brkt, 33U	2 (0.9)	13051-001	Intelligent Fan Kit	2 (0.9)									
	25190-000	Cable Port Brush Kit	2 (0.9)	40971-X72	Vertical Lashing Brkt, 40U	2 (0.9)												
	11837-701	Horizontal Wire Mgmt	4 (1.8)	11837-X02	Horizontal Wire Mgmt	4 (1.8)												
	12803-701	LED Light Kit, 4W, 120V	2 (0.9)	12803-701	LED Light Kit, 4W, 120V	2 (0.9)												