




Horizontal Rack Bonding Busbar

Use Horizontal Rack Bonding Busbar for consolidating equipment bonding. Constructed of 3/16"-thick x 3/4"H (4.763 mm x 19.1 mm) hard-drawn electrolytic tough pitch 110 alloy copper bar with eight #6-32 tapped lug mounting holes on 1" (25.4 mm) centers and two pairs of 5/16" (7.938 mm) diameter holes spaced 3/4" (19.1 mm) apart for attaching ground jumpers.

- Other configurations available on request
- UL® Listed

Part number consists of Busbar and a hardware kit that includes:

- (1) splice plate bar, 3"L (80 mm)
- (2) #12-24 copper machine screws
- (2) #12 copper flat washers
- (8) #6-32 copper machine screws
- (8) #6 ring terminals



19" rack width Busbar shown

ORDERING INFORMATION

Part Number	Description	Shipping Weight lb (kg)
10610-019	Rack Bonding Busbar, 19"W (482.6 mm) Rack	2 (0.9)
10610-023	Rack Bonding Busbar, 23"W (584.2 mm) Rack	3 (1.4)
10610-035	Rack Bonding Busbar, 35"W (889 mm) Rack	4 (1.8)

United States

Agoura Hills, CA
800-834-4969

Canada

Toronto, Ontario, Canada
+905-850-7770

Europe

Buckinghamshire, UK
+441628524834

Middle East & Africa

Dubai, UAE
+971-4-2602125

Doha, Qatar
+974-4-267422

Latin America

+52-55-5203-7525
Toll Free within Mexico
800-201-7592
chatsworth.com.co

Asia Pacific

+86 21 6880-0266
chatsworth.com.cn



CHATSWORTH
PRODUCTS