





Universal Cable Runway	UL Classified Cable Runway	Adjustable Cable Runway	Supports for Cable Runway
<p>Application: Use in telecommunication rooms, equipment rooms and data centers</p>	<p>Application: Simplifies the cable runway grounding and bonding process</p>	<p>Application: Cross Members can be easily repositioned for maximum versatility in aligning cable drops</p>	<p>Application: Connect and support Cable Runway to form a continuous pathway for cables</p>
<p>Key Features:</p> <ul style="list-style-type: none"> • UL Classified for suitability as an equipment grounding conductor only* • Remove paint to bond cable runway sections with splices or ground straps. • 9 widths • 1-1/2" H (38 mm) stringers • 12" (300 mm) cross member spacing • Powder-coated finish <p><i>*Remove paint to bond cable runway sections with splices or ground straps</i></p>	<p>Key Features:</p> <ul style="list-style-type: none"> • UL Classified for suitability as an equipment grounding conductor only • Electrical bond is achieved via Splice Kits; a separate bonding step is not required, saving on installation time. • 7 sizes • 9" (230 mm) cross member spacing • Zinc-plated finish 	<p>Key Features:</p> <ul style="list-style-type: none"> • UL Classified for suitability as an equipment grounding conductor only • Supports cable and fiber from floors, ceilings, walls and tops of cabinets and racks • Use in conjunction with other CPI Runway and accessories to form a complete pathway solution • Adapts to any data center or computer room • Ships assembled or unassembled • Powder-coated finish 	<p>Key Features:</p> <ul style="list-style-type: none"> • Support cable runway from the ceiling, wall, floor or tops of racks and cabinets • Connect Cable Runway end-to-end with Butt Splice Kits • Create 90° L- or T-shaped intersections with Junction Splice Kits • Use E-Bends and Corner Brackets to make smooth turns • Change elevations with Radius Bends • Add Cable Retaining Posts when cables are stacked over 2" H (50 mm) • Tool-less Radius Drops and Cross Members can be repositioned anywhere along the runway for maximum versatility in aligning cable drops.
<p>Widths (9):</p> <ul style="list-style-type: none"> • 4" (100 mm) • 6" (150 mm) • 9" (230 mm) • 12" (300 mm) • 15" (380 mm) • 18" (460 mm) • 24" (610 mm) • 30" (760 mm) • 36" (910 mm) 	<p>Widths (7):</p> <ul style="list-style-type: none"> • 6" (150 mm) • 9" (230 mm) • 12" (300 mm) • 15" (380 mm) • 18" (460 mm) • 20" (510 mm) • 24" (610 mm) 	<p>Widths (9):</p> <ul style="list-style-type: none"> • 4" (100 mm) • 6" (150 mm) • 9" (230 mm) • 12" (300 mm) • 15" (380 mm) • 18" (460 mm) • 24" (610 mm) • 30" (760 mm) • 36" (910 mm) 	<p>Construction:</p> <ul style="list-style-type: none"> • Welded or formed steel, zinc-plated or painted finish
<p>Length:</p> <ul style="list-style-type: none"> • 119.5" (3035 mm) 	<p>Length:</p> <ul style="list-style-type: none"> • 116.5" (2959 mm) 	<p>Length:</p> <ul style="list-style-type: none"> • 119.5" (3035 mm) 	
<p>Support Spacing:</p> <ul style="list-style-type: none"> • Load rating is 132 lb/ft with a support span of 5' (1.5 m) 	<p>Support Spacing:</p> <ul style="list-style-type: none"> • Load rating is 132 lb/ft with a support span of 5' (1.5 m) 	<p>Support Spacing:</p> <ul style="list-style-type: none"> • Load rating is 132 lb/ft with a support span of 5' (1.5 m) 	
<p>Construction:</p> <ul style="list-style-type: none"> • Welded steel, painted finish 	<p>Construction:</p> <ul style="list-style-type: none"> • Welded steel, zinc plated finish 	<p>Construction:</p> <ul style="list-style-type: none"> • Roll-formed Steel Stringers • Aluminum Cross Members • Painted finish 	



Universal Cable Runway

UL Classified Cable Runway

Adjustable Cable Runway

Supports for Cable Runway

Part No.	Description	Wt. lb (kg)
10250-X04	1.5"H x 4"W x 9'-11.5"L 38 mm x 100 mm x 3 m	18 (8.2)
10250-X06	1.5"H x 6"W x 9'-11.5"L 38 mm x 150 mm x 3 m	19 (8.6)
10250-X09	1.5"H x 9"W x 9'-11.5"L 38 mm x 230 mm x 3 m	20 (9.1)
10250-X12	1.5"H x 12"W x 9'-11.5"L 38 mm x 300 mm x 3 m	25 (11.3)
10250-X15	1.5"H x 15"W x 9'-11.5"L 38 mm x 380 mm x 3 m	27 (12.2)
10250-X18	1.5"H x 18"W x 9'-11.5"L 38 mm x 460 mm x 3 m	29 (13.2)
10250-X24	1.5"H x 24"W x 9'-11.5"L 38 mm x 610 mm x 3 m	32 (14.5)
10250-X31	1.5"H x 30"W x 9'-11.5"L 38 mm x 760 mm x 3 m	35 (15.7)
10250-X37	1.5"H x 36"W x 9'-11.5"L 38 mm x 910 mm x 3 m	38 (17.2)

Note: X=Color: 1=Gray, 2=Computer Beige, 7=Black, E=Glacier White.

Key Accessories

Part No.	Description	Wt. lb (kg)
11301-001	Butt-Splice Kit	1 (0.5)
11302-001	Junction-Splice Kit	1 (0.5)
40164-025	Ground Strap Kit Pack of 25	12 (5.0)
11959-X15*	Corner Bracket, 15"W (380 mm)	4 (1.8)
10822-X12*	E-Bend, 12"W (300 mm)	12 (5.4)
10596-X56*	Cable Retaining Post, 6"H (150 mm), Pack of 50	33 (15.0)
10642-001	Protective End Caps	1 (0.5)
25400-X00	Touch-Up Paint, Spray Can, 12 oz (340)	2 (0.9)
13395-X04*	Patch Rack, 4U x 19"W w/Side Stringer Brackets	5 (2.3)

Note: X=Color: 1=Gray, 2=Computer Beige, 7=Black, E=Glacier White.

*Additional sizes available.

Part No.	Description	Wt. lb (kg)
11275-X06	1.5"H x 6"W x 9'-8.5"L 38 mm x 150 mm x 2.9 m	19 (8.6)
11275-X09	1.5"H x 9"W x 9'-8.5"L 38 mm x 230 mm x 2.9 m	20 (9.1)
11275-X12	1.5"H x 12"W x 9'-8.5"L 38 mm x 300 mm x 2.9 m	22 (10.0)
11275-X15	1.5"H x 15"W x 9'-8.5"L 38 mm x 380 mm x 2.9 m	26 (11.8)
11275-X18	1.5"H x 18"W x 9'-8.5"L 38 mm x 460 mm x 2.9 m	28 (12.7)
11275-X20	1.5"H x 20"W x 9'-8.5"L 38 mm x 510 mm x 2.9 m	29 (13.2)
11275-X24	1.5"H x 24"W x 9'-8.5"L 38 mm x 610 mm x 2.9 m	31 (14.1)

X=Color over Zinc: 0=Gold, 7=Black.

Key Accessories

Part No.	Description	Wt. lb (kg)
16301-001	Butt-Splice Kit	1 (0.5)
16302-001	Junction-Splice Kit	1 (0.5)
11959-X15*	Corner Bracket, 15"W (380 mm)	4 (1.8)
10822-X12*	E-Bend, 12"W (300 mm)	12 (5.4)
10723-X12*	Outside Radius Bend, 12"W (300 mm)	4 (1.8)
10724-X12*	Inside Radius Bend, 12"W (300 mm)	4 (1.8)
10596-X58*	Cable Retaining Post, 8"H (200 mm), Pack of 50	33 (15.0)
13395-X04*	Patch Rack, 4U x 19"W w/Side Stringer Brackets	5 (2.3)

Note: X=Color: 1=Gray, 2=Computer Beige, 7=Black, E=Glacier White.

*Additional sizes available.

Part No.	Description	Wt. lb (kg)
14300-X04	1.5"H x 4"W x 119.5"L 38 mm x 102 mm x 3035 mm	17 (8.0)
14300-X06	1.5"H x 6"W x 119.5"L 38 mm x 152 mm x 3035 mm	18 (8.2)
14300-X09	1.5"H x 9"W x 119.5"L 38 mm x 229 mm x 3035 mm	19 (8.6)
14300-X12	1.5"H x 12"W x 119.5"L 38 mm x 305 mm x 3035 mm	20 (9.1)
14300-X15	1.5"H x 15"W x 119.5"L 38 mm x 381 mm x 3035 mm	21 (9.8)
14300-X18	1.5"H x 18"W x 119.5"L 38 mm x 457 mm x 3035 mm	22 (10.9)
14300-X24	1.5"H x 24"W x 119.5"L 38 mm x 610 mm x 3035 mm	25 (11.0)
14300-X30	1.5"H x 30"W x 119.5"L 38 mm x 762 mm x 3035 mm	27 (12.0)
14300-X36	1.5"H x 36"W x 119.5"L 38 mm x 914 mm x 3035 mm	30 (13.0)

X=Color: 1=Gray, 2=Computer Beige, E=Glacier White, 7=Black.

Key Accessories

Part No.	Description	Wt. lb (kg)
14308-001	Tool-less Pathway Divider Pack of 10	2 (1.0)
14304-X12*	Tool-less Cross Member Radius Drop, 12"W (300 mm)	2 (1.0)
14305-X00	Tool-less Stringer Radius Drop, Large	3 (1.0)
14305-X01	Tool-less Stringer Radius Drop, Small	2 (1.0)
14302-X12*	Cross Member Kit, 12"W (300 mm)	4 (2.0)
14303-X10	Stringer Kit, 1.5"H x 0.4"W x 119.5"L 38 mm x 10 mm x 2025 mm	69 (31)

Note: X=Color: 1=Gray, 2=Computer Beige, 7=Black, E=Glacier White.

*Additional sizes available.

Contact Tech Support at 800-834-4969 for assistance specifying splices and supports.

Part No.	Description	Wt. lb (kg)
Triangle Support Bracket		
11746-X12	Wall Support, Side, for 12"W (300 mm) Runway	5 (2.3)
11746-X18	Wall Support, Side, for 18"W (460 mm) Runway	8 (3.6)
11746-X24	Wall Support, Side, for 24"W (610 mm) Runway	9 (4.1)
Wall Angle Support Kit		
11421-X12	Wall Support, End, for 12"W (300 mm) Runway	3 (1.4)
11421-X18	Wall Support, End, for 18"W (460 mm) Runway	5 (2.3)
11421-X24	Wall Support, End, for 24"W (610 mm) Runway	6 (2.7)

Center Support Kit

12362-X12	Ceiling Support, for 12"W (300 mm) Runway	2 (0.9)
12362-X18	Ceiling Support, for 18"W (460 mm) Runway	4 (1.8)
12362-X24	Ceiling Support, for 24"W (610 mm) Runway	5 (2.3)

3" Channel Rack-To-Runway Mounting Plate

10595-X12	Rack-Top Support, for 12"W (300 mm) Runway	5 (2.3)
10595-X18	Rack-Top Support, for 18"W (460 mm) Runway	7 (3.2)
12408-X24*	Rack-Top Support, for 24"W (610 mm) Runway	4 (1.8)

Additional sizes available. Use with CPI Standard and Universal Racks.

Cable Runway Elevation Kits

10506-X02	Elevates Runway, 2"H (50 mm), 2.5"H (64 mm)	2 (0.9)
-----------	--	---------

*Use with Rack-To-Runway Mounting Plate.

60508-X02	Supports Two Tiers, Elevates Runway, 2-3"H (50-75 mm), Black & Glacier White	5 (2.3)
-----------	--	---------

Note: X=Color: 0=Gold, 1=Gray, 2=Computer Beige, 7=Black, E=Glacier White. *12408-024 not available

Contact Tech Support at 800-834-4969 for assistance specifying splices and supports.

chatsworth.com • techsupport@chatsworth.com • 800-834-4969



Visit chatsworth.com for more information on our pathway products and a complete part number listing.

While every effort has been made to ensure the accuracy of all information, CPI does not accept liability for any errors or omissions and reserves the right to change information and descriptions of listed services and products.
©2023 Chatsworth Products, Inc. All rights reserved. Chatsworth Products, Clik-Nut, CPI, CPI Passive Cooling, CUBE-IT, Secure Array, eConnect, Evolution, GlobalFrame, MegaFrame, QuadraRack, RMR, Saf-T-Grip, SeismicFrame, SlimFrame, TeraFrame, Motive and Velocity are federally registered trademarks of Chatsworth Products. EuroFrame, H-Plane, Hi-Bar, In-Plane, M-Frame, NetPoint, Oberon, Simply Efficient, Skybar, Wi-Tile and ZetaFrame are trademarks of Chatsworth Products. All other trademarks belong to their respective companies. Rev 7 05/23 MKT-60020-292